

#### THE POCKET-SIZED WIRELESS ENTERPRISE-CLASS 1D/2D SCANNER FOR CARTS AND MORE.

# **SYMBOL CS4070-HC**

#### Put advanced bar code scanning in the pockets of your healthcare workers to improve patient safety and the patient experience.

Bar code scanning at patient bedside is crucial in preventing deadly errors in medication administration and specimen collection. Now, you can keep enterprise-class bar code capture at the fingertips of every nurse and lab technician with the CS4070-HC. This little wireless enterprise-class bar code scanner is designed for the mission critical world of the healthcare worker. Small enough to be easily carried at all times, it can be tucked in a pocket or worn on a lanyard. Superior scanning technology means your healthcare workers can dependably scan any electronic or printed 1D or 2D bar code in any condition in the time it takes to press the scan button, whenever and wherever required. With the press of the dedicated pairing button, this flexible Bluetooth scanner is easily paired with in-room computers and computers-on-wheels (COWs) — or even tablets. Add its rugged disinfectant-ready design that prevents the spread of germs, full shift power, user-selectable scanning feedback and superior ergonomics, and the CS4070-HC is the ideal individual scanning companion for your healthcare workers.



#### PRZM Intelligent Imaging technology for next generation bar code scanning performance — only from Motorola

Delivers laser-style speed and accuracy for first-time every time split second capture of 1D and 2D printed bar codes in virtually any condition — even if they are dirty, scratched or poorly printed.

### Scan virtually any bar code on any medium

Scans 1D, 2D and PDF417 bar codes displayed on a screen or printed on paper labels, as well as the tiny bar codes printed on individual medication doses and bar codes on curved, reflective surfaces, such as vials, syringes, IV bags, suppositories and patient wristbands.

#### **Superior ergonomics**

One of the smallest and lightest devices in its class, the CS4070-HC can be tucked in a pocket or worn around the neck on a lanyard. Grooves guide the hand to the most comfortable placement and provide a secure grip, and the placement of trigger buttons enables effortless scanning with any size hand.

#### **Easy Bluetooth pairing**

One press of the dedicated pairing button connects the CS4070-HC to virtually any Bluetooth-enabled device — from tablets and laptops to in-room computers and COWs.

#### Withstands constant disinfecting

IP52 sealing and a specially designed disinfectant-ready plastic housing allow safe wipe-down with a wide variety of harsh chemicals to help prevent the spread of germs.

#### Durable design — built to be dropped

Operates reliably after 5 ft./1.2 m drops and 500 consecutive "tumbles" from 1.64 ft./0.5 m.

#### One million+ scans for superior value

The scan button and scan button graphics are designed and tested to handle over a million presses.

#### Full-shift power — period

In the mission-critical world of healthcare, users count on full-shift operation. That's why the field replaceable battery can be easily changed on-the-go and is designed to last an entire busy 12-hour shift, with an LED indicator that alerts the user when a battery change is needed.

#### Day and night 'do-not-disturb' modes

Healthcare workers can choose to mix and match the decode feedback that is right for the moment: visual (green light/red light), haptic (vibration) and an audible tone.

#### Point-and-shoot scanning simplicity

Bar code capture is easy. An extraordinarily wide working range combined with omnidirectional scanning eliminates the need to align scanner and bar code — no need to disturb a sleeping patient to capture the bar code on a wristband.

# With Service from the Start Advance Exchange with Comprehensive Coverage, your CS4070-HC scanners are covered — period.

This optional service plan keeps devices up, running and in like-new condition with coverage for accidental damage and everyday wear-and-tear — all for just pennies a day.

## GIVE YOUR HEALTHCARE WORKERS THE POCKETABLE 1D/2D BAR CODE SCANNING THEY NEED TO IMPROVE PATIENT SAFETY — AND THE PATIENT EXPERIENCE.

For more information, visit www.motorolasolutions.com/cs4070hc or access our global contact directory at www.motorolasolutions.com/contactus

### **CS4070-HC SPECIFICATIONS CHART**

Dimensions	4.39 in. L x 1.79 in. W x 1.02 in. H			
	11.15 cm L x 4.55 cm W x 2.6 cm H			
Weight	With batteries: 3.28 oz./93.2 g			
Scan Engine	SE4710 image engine			
Memory	512 MB Flash			
Memory Capacity	Over 1 million barcodes (UPC with time date stamp)			
LEDs	Scan LED (Green, Red, and Amber) and Bluetooth® LED (Blue) Four LED battery status indicator			
Buttons	Scan, remove scan (batch mode only), enable Bluetooth (RF scanners only), battery status; scan button tested to a million depressions, all other buttons tested to 250,000 depressions			
OPERATING MODES				
Batch	Scans recorded with optional time/date stamp			
Open Bluetooth	Real time wireless data transmission			
BATTERY				
Battery	950 mAh Lithium ion			
Charge Time	3 hours 40 minutes			
Battery Life	Batch: 24 hours use or 8,500 scans (6 scans per minute on full charge)			
	Standby: 3 months Bluetooth 12 hours use or 4,250 scans (6 scans per minute on full charge)			
Power Consumption	5V, 500mA max while charging			
PERFORMANCE CHA	RACTERISTICS			
Decode Capability	1D and 2D symbologies			
Interfaces Supported	USB (micro jack): Bluetooth			
Real Time Clock	A date/time stamp can be recorded with each bar code scanned (batch mode operation only)			
Batch Communication	USB 2.0			
	USB 2.0			
USER ENVIRONMEN	USB 2.0			
USER ENVIRONMENTO Specification	USB 2.0 T			
Batch Communication  USER ENVIRONMENT  Drop Specification  Tumble Specification  Sealing	USB 2.0  T  Multiple 5 ft./1.5 m drops to concrete			
USER ENVIRONMENT Drop Specification Tumble Specification	USB 2.0  T  Multiple 5 ft./1.5 m drops to concrete 250 cycles @ 1.64 ft./0.5 m (500 drops)			
USER ENVIRONMENT Drop Specification Tumble Specification Sealing Operating	USB 2.0  T  Multiple 5 ft./1.5 m drops to concrete 250 cycles @ 1.64 ft./0.5 m (500 drops) IP52, disinfectant ready			

Ambient Lighting Tolerance	Tolerant to typical artificial indoor and natural outdoor (direct sunlight) lighting conditions. Fluorescent, Incandescent, Mercury Vapor, Sodium Vapor, LED1: 450 ft. candles (4,844 Lux) Sunlight: 8,000 ft. candles (86,111 Lux)
BLUETOOTH	
Bluetooth Radio	Bluetooth, Class 1/Class 2, Version 2.1 + Enhanced Data Rate (EDR)
Bluetooth Range	300 ft./100 m when configured for Class 1 or 30 ft./10 m when configured for Class 2
Bluetooth Profiles	HID keyboard wedge and Serial Port Profile (SPP) and Wireless SSI (proprietary)

BT-CS1-0BR Bluetooth Dongle for Bluetooth Class 1 Version 2.0 enables connection to host by simply scanning a barcode; CHS5000-1000CR Charge Cradle charges one scanner and one battery simultaneously; CHS5000-8000CR Charge Cradle charges up to eight scanners; SAC5000-8000CR Charge Cradle charges up to eight batteries; lanyard

REGULATORY	
Laser Safety	IEC62471:2006 (Ed.1.0); EN62471:2008 (LED)
EMC	FCC Part 15 Class B, ICES 003 Class B, EN 55022, EN 55024, EN 301 489-1, EN 301 489-17
Radio	EN 300 328
Electrical Safety	UL 60950-1, C22.2 No. 60950-1, EN 60950-1, IEC 60950-1
Environmental	EN50581
WARRANTY	

#### WAIIIIAITT

Warranted against defects in workmanship and materials for a period of thirty-six (36) months

D	E	0	D	E	R	A٨	IG	E

5 mil Code 128:       2.4 in. / 6.1 cm — 7.8 in. / 19.8 cm         5 mil 39:       1.6 in. / 4.1 cm — 13.1 in. / 33.3 cm         5 mil PDF417:       2.7 in. / 6.9 cm — 8.0 in. / 20.3 cm         10 mil Data Matrix:       2.5 in. / 6.4 cm — 9.7 in. / 24.7 cm         100% UPCA:       1.4 in. / 3.6 cm* — 25.6 in. / 65.0 cm         20.0 mil Code 39:       1.6 in. / 4.1 cm* — 29.6 in. / 75.2 cm	4 mil Code 39:	2.9 in. / 7.4 cm — 8.4 in. / 21.4 cm
5 mil PDF417: 2.7 in. / 6.9 cm — 8.0 in. / 20.3 cm  10 mil Data Matrix: 2.5 in. / 6.4 cm — 9.7 in. / 24.7 cm  100% UPCA: 1.4 in. / 3.6 cm* — 25.6 in. / 65.0 cm  20.0 mil Code 39: 1.6 in. / 4.1 cm* — 29.6 in. / 75.2 cm	5 mil Code 128:	2.4 in. / 6.1 cm — 7.8 in. / 19.8 cm
10 mil Data Matrix: 2.5 in. / 6.4 cm — 9.7 in. / 24.7 cm 100% UPCA: 1.4 in. / 3.6 cm* — 25.6 in. / 65.0 cm 20.0 mil Code 39: 1.6 in. / 4.1 cm* — 29.6 in. / 75.2 cm	5 mil 39:	1.6 in. / 4.1 cm — 13.1 in. / 33.3 cm
100% UPCA: 1.4 in. / 3.6 cm* — 25.6 in. / 65.0 cm 20.0 mil Code 39: 1.6 in. / 4.1 cm* — 29.6 in. / 75.2 cm	5 mil PDF417:	2.7 in. / 6.9 cm — 8.0 in. / 20.3 cm
20.0 mil Code 39: 1.6 in. / 4.1 cm* — 29.6 in. / 75.2 cm	10 mil Data Matrix:	2.5 in. / 6.4 cm — 9.7 in. / 24.7 cm
	100% UPCA:	1.4 in. / 3.6 cm* — 25.6 in. / 65.0 cm
	20.0 mil Code 39:	1.6 in. / 4.1 cm* — 29.6 in. / 75.2 cm
*Minimum distance determined by symbol length and scan angle		

#### **SERVICES**

Enjoy easy access to fast repair and expert support with Service from the Start. Add "next business day" replacement with Advanced Exchange.

#### **APPLICATIONS**

- Medication administration
- Transfusion administration
- Specimen labeling
- Specimen tracking
- Medication tracking at the dose level in the hospital pharmacy
- Inventory takes in individual floor supply cabinets for timely replenishment

Part number: SS-CS4070HC. Printed in USA 07/14. MOTOROLA, MOTO, MOTOROLA SOLUTIONS, the Stylized M logo and Symbol are trademarks or registered trademarks of Motorola Trademark Holdings, LLC and are used under license. All other trademarks are the property of their respective owners. ©2014 Motorola Solutions, Inc. All rights reserved.



